

GRAS 43BA-2

1/4" 0.4cc CCP High
Frequency Coupler Kit



Connection: CCP
Volume: 0.4cc
IEC: TS 62886 (IEC 60118-0)
Use: For hearing aid test up to 16 kHz

The GRAS 43BA-2 is a 1/4" 0.4cc High frequency coupler for test of hearing aids. It uses a 1/4" microphone and 1/4" preamplifier with CCP connection. The equivalent externally polarized version is GRAS 43BA-1.

Introduction

The GRAS 43BA-2 is a high frequency 1/4" 0.4cc coupler kit for test of hearing aids at frequencies up to 16 kHz. It is a complete kit with a 1/4" Pressure Microphone and a 1/4" Preamplifier with BNC connection and the same adapters known from the reference 2cc coupler. It is easy and safe to handle and calibrate because the microphone grid does not have to be removed for mounting or calibration.

Typical applications and use

It is designed in accordance with the Technical Specification "IEC TS 62886:2016 Electroacoustics - Hearing aids - Method for measuring electroacoustic performance up to 16 kHz". It meets the need for an accurate and repeatable measurement method that can be used by designers of hearing aids and hearing aids receivers, and by fitters of hearing aids. IEC TS 62886 can be bought from the IEC webstore,

<https://webstore.iec.ch/publication/25718>.

The small volume in combination with the 1/4" microphone results in a wide frequency range that makes it useful for high-frequency diagnostics. The extended frequency range also ensures that it is a future proof choice for high-frequency testing of wide-band hearing aids.

Its 0.4cc volume is a well defined cylinder where the diaphragm of the microphone is flush with the bottom of the cylinder. The cylinder is machined to within $\pm 2\%$ of the nominal 0.4cc volume. The exact volume for each individual coupler is stated in the accompanying calibration chart. The performance of the 0.4cc coupler can therefore be accurately simulated, and it can easily be a part of a complete simulation model.

The 43BA is designed for repetitive use and is equally suited for research, quality assurance and production test applications.

Design

The 43BA is developed with and for the hearing aids industry. Through our close collaboration with global leaders within the industry, we found an increasing need for test of modern hearing aids at high frequencies. In accordance with the intentions of the previously mentioned IEC Technical Specification GRAS has designed a coupler kit capable of delivering differentiated and reproducible data up to 16 kHz.

Because of the small volume, the measured sound level from the 0.4cc coupler is 13.5 dB higher than with a 2cc coupler. This increase in level improves the signal-to-noise ratio compared to what is normally achievable with the 1/4" microphone used.

Another benefit of the small volume and the 1/4" microphone is the fact that the resonance frequency at 30 kHz is so high that it does not interfere with measurements in the audible frequency range. Therefore it can be used for measurements up to 16 kHz, one octave higher than achievable with the standardized 2cc coupler.

The 43BA-2 is designed to perform optimally with the [GRAS 40BD](#) Prepolarized Pressure Microphone, which is ideally suited for sound measurements at high levels and high frequencies. It has a wide dynamic range for measuring sound pressure levels up to 168 dB. The preamplifier is the [GRAS 26CS](#) CCP Standard Preamplifier, Very Short. The 26CS is a small robust unit short enough for use in confined spaces like anechoic test chambers. It has a very low inherent-noise level, a wide dynamic range and a frequency response from below 2 Hz to above 200 kHz.

The microphone set is locked and kept firmly in position by a very precise locking mechanism, that automatically centers and locks the microphone at the same time, eliminating the risk of measurement

errors caused by incorrect positioning of the microphone. An O-ring ensures a tight sealing of the microphone. The microphone set can easily be removed for sensitivity calibration – without tools. There is never any need for removing the protective grid, neither for use, calibration or other handling of the microphone.

Compatibility

The GRAS 43BA-2 requires a power module or measurement instrumentation input that that can provide a constant current of app. 4 mA. The microphone set requires a Microdot-BNC cable that is part of the delivery. Various extension cables are available. The 0.4cc coupler housing fits all GRAS 1/2" 2cc standard ear mould and tube adapters.

System verification

For daily verification and check of your measurement setup we therefore recommend using a sound source like the GRAS 42AB Sound Calibrator. For proper sensitivity calibration we recommend using a reference sound source like the GRAS 42AP Intelligent Pistonphone.

Performance and warranty

GRAS microphone sets and couplers are all manufactured of high-quality materials and brand parts that were chosen and processed to ensure life-long stability and robustness.

All parts are manufactured and assembled at the factory in Denmark by skilled and dedicated operators in verified clean-room environments. The microphone diaphragm, body and unique protection grid are made of high-grade stainless steel and make the microphone set resistant to physical damage as well as corrosion caused by aggressive air or gasses.

This, together with the reinforced gold plated microphone terminal which guarantees a highly

reliable connection, enables us to offer 5 years warranty against defective materials and workmanship.

The warranty for cables is 6 months.

Theoretical dynamic range lower limit with GRAS preamplifier	dB(A)	44
Theoretical dynamic range upper limit with GRAS preamplifier @ +28 V / ±14 V power supply	dB	166
Set sensitivity @ 250 Hz (±3 dB)	mV/Pa	1.45
Set sensitivity @ 250 Hz (±3 dB)	dB re 1V/Pa	-57
Coupler volume	mm ³	0.4 ccm
Resonance frequency	kHz	30
Temperature range, operation	°C / °F	-30 to 60 / -22 to 140
Temperature coefficient @250 Hz	dB/°C / dB/°F	-0.01
Humidity range non condensing	% RH	0 to 80
CE/RoHS compliant/WEEE registered		Yes/Yes/Yes
Connector type		Microdot 10/32
Weight	g / oz	50 / 1.76

GRAS Sound & Vibration reserves the right to change specifications and accessories without notice.

Included

GRAS RA0252	0.4cc Coupler
GRAS 40BD	¼" Prepolarized Pressure Microphone, High levels
GRAS 26CS	¼" CCP Preamplifier with Microdot Connector, Very Short
GRAS AA0070	3 m Cable Microdot-BNC
GRAS RA0270	Ear-mould Adapter Kit for RA0038 / RA0252 Couplers
GRAS RA0271	Tube Adapter for RA0038 / RA0252
GRAS RA0272	In-Ear Adapter for RA0038 / RA0252 Couplers

Optional

GRAS AA0035	3-m BNC extension cable
GRAS AG0002	CCP Input Adapter
GRAS 12AL	1-Channel CCP Power Module with A-weighting Filter
GRAS 12AQ	2-Channel CCP/LEMO Power Module with Signal Conditioning and Computer Interface
GRAS 42AP	Intelligent pistonphone
GRAS 42AG	Multifunction Sound Calibrator

GRAS Sound & Vibration reserves the right to change specifications and accessories without notice.

GRAS Worldwide

Subsidiaries and distributors in more
than 40 countries

HEAD OFFICE, DENMARK
GRAS SOUND & VIBRATION
Skovlytoften 33
2840 Holte
Denmark
Tel: +45 4566 4046
www.gras.dk
gras@gras.dk

USA
GRAS SOUND & VIBRATION
5750 S.W. Arctic Drive
Beaverton, OR 97005
Tel: 503-627-0832
Toll Free: 800-231-7350
www.gras.us
sales@gras.us

CHINA
GRAS SOUND & VIBRATION
Room 303, Building T6
Hongqiaohui, 990, Shenchang Road
Minhang District, Shanghai
China, 201106
Tel: +86 21 64203370
www.gras.com.cn
cnsales@gras.dk



ABOUT GRAS SOUND & VIBRATION

GRAS is a worldwide leader in the sound and vibration industry. We develop and manufacture state-of-the-art measurement microphones to industries where acoustic measuring accuracy and repeatability is of utmost importance in R&D, QA and production. This includes applications and solutions for customers within the fields of aerospace, automotive, audiology, and consumer electronics. GRAS microphones are designed to live up to the high quality, durability and accuracy that our customers have come to expect and trust.

GRAS Sound
& Vibration